



## TECHNICAL DATA

Item no.	1006876
Number of different light outlets	1
Assembly	Recessed
Assembly details	Ceiling
Secondary power / voltage	200 mA
Safety class	III
Minimum ambient temperature	-20 °C
Maximum ambient temperature	40 °C
Lumen	640 lm
Colour temperature	2700 Kelvin
Beam angle	20 °
Color	white
CRI	90
UGR ≤	16
LXXBXX data	L80B50
Risk Group	1
Length	8 cm
Diameter	4.9 cm
Net weight	0.24 kg
Gross weight	0.257 kg
Shape of cut-out	round
Installation depth	10 cm

## Light Source

798300	
--------	---

Installation diameter	6.8 cm
-----------------------	--------

## Accessories

1005609	LED Driver , 200mA 10W PHASE, Quick Connector
1005610	LED Driver , 200mA 10-W, Quick Connector
1005611	LED Driver , 200mA 13,5W DALI dimmable, Quick Connector
1005612	NUMINOS® XS , diffuser
1005613	NUMINOS® XS , transparent diffuser
1005614	NUMINOS® XS , frosted diffuser
1005615	NUMINOS® XS , black diffuser