

[Products](#) [Power Supplies](#) [DC switching mode power supplies \(3A to 60A\)](#) [PeakTech® 6225 A](#)

PeakTech® 6225 A PROD-ID: P 6225 A

[BACK](#)

Laboratory Switching Mode Power Supply DC 0 - 30 V/0 - 5 A

This switching mode power supply is ideal of its very handy shape and low weight for applications in the development and education area.

The high visibility of the display, the easy operation and low weight, as well as the slim design are excellent conditions for use in education and service area.

- Blue LED display to show the output voltage - and current values
- High efficiency >85%
- Low ripple & noise
- Protection against short circuit, overload and over-temperature
- Adjustable voltage range: 0 ~ 30 V
- Safety: EN 61010-1
- Accessories: Power cable and manual



MANUAL

[PeakTech 6225A 06 2016.pdf \(493.7 kB\)](#)

PICTURES

[6225A Front Freigestellt.jpg \(241.9 kB\)](#)

[6225A L Freigestellt.jpg \(258.2 kB\)](#)

[6225A R Freigestellt.jpg \(226.7 kB\)](#)

Output voltage (fixed)	0 ~ 30 V DC
Output current	0 ~ 5 A DC
Ripple & noise	≤ 3 mV RMS; ; ≤ 3 mA RMS
Load regulation	≤ 0.01% + 5 mV
Line regulation	≤ 0.01% + 1 mV
Display accuracy	+/- 0,1% + 2 dgt.
Protection	Overload, overtemperature, short circuit protections by constant current circuitry and output overvoltage
Operating voltage	110 ~ 240 V AC; 50/60 Hz
Dimensions (WxHxD)	78 x 160 x 255 mm
Weight	2,6 kg
EAN-13	4250569403910

