

# Blade Terminals




## FEATURES:

Vinyl-insulated  
 Double crimp  
 Male Disconnects  
 PVC  
 Funnel entry

## SPECIFICATION:

Material	Brass
Insulation material	Vinyl
Surface material	Tin-plated
Temperature range	max. +105 °C



UL certified: E502428

## PRODUCT RANGE:

Article Nr.	Colour	Contact	Cross-section	D	L	t1	B	E
RND 465-00523	Red	2.8 x 0.5 mm	0.5...1.5 mm <sup>2</sup>	4.1 mm	22 mm	0.8 mm	2.9 mm	10.5 mm
RND 465-00524	Red	4.8 x 0.5 mm	0.5...1.5 mm <sup>2</sup>	4.1 mm	22 mm	0.8 mm	4.8 mm	10.5 mm
RND 465-00525	Red	4.8 x 0.8 mm	0.5...1.5 mm <sup>2</sup>	4.1 mm	22 mm	0.8 mm	4.8 mm	10.5 mm
RND 465-00526	Red	6.3 x 0.8 mm	0.5...1.5 mm <sup>2</sup>	4.1 mm	22 mm	0.8 mm	6.3 mm	10.5 mm
RND 465-00527	Blue	4.8 x 0.8 mm	1.5...2.5 mm <sup>2</sup>	4.9 mm	22.5 mm	0.8 mm	4.8 mm	11 mm
RND 465-00528	Blue	6.3 x 0.8 mm	1.5...2.5 mm <sup>2</sup>	4.9 mm	22.5 mm	0.8 mm	6.3 mm	11 mm
RND 465-00529	Yellow	6.3 x 0.8 mm	4...6 mm <sup>2</sup>	6.5 mm	24.5 mm	0.8 mm	6.3 mm	13.5 mm
RND 465-00530	Red	2.8 x 0.8 mm	0.5...1.5 mm <sup>2</sup>	4.1 mm	22 mm	0.8 mm	2.9 mm	10.5 mm