


# control block for two-hand start ZSB-1/8-B

Part number: 576656

FESTO



## Data sheet

Feature	Value
Nominal size	4 mm
Type of actuation	pneumatic
Assembly position	Any
Safety function	Two-hand operation
Performance level (PL)	Two-hand operation/Cat. 1, PLC
Operating pressure	4 ... 8 bar
Standard nominal flow rate	50 l/min
CE mark (see declaration of conformity)	to EU directive for machinery
Certificate issuing department	IFA 1201046
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	0 ... 60 °C
Product weight	420 g
Mounting type	with through hole with internal (female) thread Optional
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	G1/8
Materials note	Conforms to RoHS
Material cover	Aluminium die cast
Material seals	NBR
Material housing	Wrought Aluminium alloy Anodised