



Part no.: 50122338
KB DN/CAN-10000 SBA
Interconnection cable




Figure can vary

Contents

- Technical data
- Electrical connection

Technical data

Basic data

Suitable for interface	CANopen DeviceNet
------------------------	----------------------

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Connection 2

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Cable properties

Number of conductors	5 Piece(s)
Sheathing color	Black
Shielded	Yes
Cable design	Interconnection cable
Cable diameter (external)	7 mm
Cable length	10,000 mm
Sheathing material	PUR

Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection

Connection 1	
Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Part no.: 50122338 – KB DN/CAN-10000 SBA – Interconnection cable

Connection 2	
Type of connection	Connector
Thread size	M12
Type	Female
Handle body material	
No. of pins	5 -pin
Encoding	A-coded
Design	Axial
Lock	