

Accessory

PICO-LPG-405-532-BOX
Order Number: 70143348

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-20		40	°C
Storage Temperature	-50		50	°C

Optical Parameters

LB Rating	180-315 D LB7 + IR LB4, >315-532 DIRM LB6
Lens Color	Orange

Mechanical Parameters

Material	Plastic
Weight	150 g

(*) Over the complete operating temperature range

Features



- Laser glasses for blue and green wavelengths
- Incl. wall holder
- Stickers with mandatory and hazard sign

Picture



Safety Label



Valid Revision

| 28-OCT-2020