

# Zero Smog 6V with gas filter

Product no.: T0053667699N



## Benefits

- › The Constant Flow Control (CFC) guarantees optimal air flow regulation for each working place independent of the connected workplaces
- › Efficiency test via USB port
- › Electronic filter control with optical and acoustical filter alarm
- › 4 wheels to allow easy movement of the unit
- › Remote control via RS 232 port
- › Low noise level
- › The fume extraction system Zero Smog 6V with gas filter could be used to extract adhesive fumes. The unit is user-friendly with quick and simple installation and filter exchange. It has a low noise emission level and is small and convenient to locate within the work area. The high quality components used in the ZS 6V result in low servicing requirements and long system life. To increase filter lifetime and save on energy, the ZS 6V is fitted with a constant flow control (CFC) – depending on the number of connected workplaces. To extend the capacity an external.

For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning



Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	460 x 460 x 665
Dimensions L x W x H (inches)	18,11 x 18,11 x 26,18
Weight (approx.) in kg	40
Voltage	230 V, 50/60 Hz
Power	460 VA
Noise level (distance 1 m) dB(A)	51
Max. vacuum	---
Capacity m³/h	615
Pre-filter	Pre filter mat class F7
Compact filter	Particle filter H13, Wide band gas filter (50 % Active carbon / 50 % Chemisorb)
Max. capacity	1-8 workstations
RS232 interface (remote control)	All system functions can be operated and remotely monitored via the RS232 port.
USB port	on
WX-compatible	on

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE