

# Multimar electronic universal measuring instrument

25 EWRI



## Application:

For universal measurement of diverse tasks, e.g. external and internal measurement of bores, threads, tothing, recesses, grooves etc.

## Execution:

- ON/OFF
- Zero setting at any position
- mm/inch changeover
- AUTO OFF
- Preset function
- Extensive accessories: Measuring arm probe tips, stops (optional)
- Both measuring arm holders are movable

## Advantage:

- Unrestricted freedom of movement (radio range up to 6 m)

## Delivery:

Battery, operating instructions, assembly and storage blocks, wooden box (without gauge slides)



<b>Art. no.</b>	<b>31901 030</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4119052
<b>Min./max. external length measuring range</b>	0-1000 mm
<b>Battery included</b>	Yes
<b>Type of rechargeable battery/battery</b>	Lithium
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>IP protection class</b>	IP 65
<b>Gross Weight</b>	1.600 kg
<b>Product Group</b>	305