



## Master LEDtube HF 1200mm HE 16.5W 830 T5

The Philips MASTER LEDtube integrates an LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescents. These T5 lighting tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings, thanks to low energy consumption and an exceptionally long lifetime, make these T5 LED tubes the choice for every demanding applications.

#### **Product data**

General information					
Cap base	G5 [G5]				
Nominal lifetime	60,000 h				
Switching Cycle	50,000				
Lighting Technology	LED				
Flux measurement reference	Sphere				
Light technical					
Colour Code	830 [CCT of 3000K]				
Beam angle (nom.)	200 degree(s)				
Luminous Flux	2,300 lm				
Colour designation	White (WH)				
Correlated Colour Temperature	3000 K				
Luminous Efficacy (rated) (Nom)	139.00 lm/W				
Colour consistency	<6				
Colour rendering index (CRI)	80				
LLMF at end of nominal lifetime (nom.) 70 %					


Operating and electrical					
Line Frequency	30K to 100K Hz				
Input frequency	30 K to 100 K Hz				
Power Consumption	16.5 W				
Starting time (nom.)	0.5 s				
Warm-up time to 60% light	0.5 s				
Power Factor (Fraction)	0.92				
Voltage (nom.)	70-120 V				
Temperature					
T-Case maximum (nom.)	65 ℃				
Controls and dimming					
Dimmable	Yes – Check ballast compatibility				
Mechanical and housing					
Lamp Finish	Frosted				
Bulb material	Glass				
·					

Datasheet, 2023, April 14 data subject to change

Product length	1,200 mm				
Bulb shape	Tube, double-ended				
Approval and application					
Energy-saving product	Yes				
Approval marks	RoHS compliance TUV CE marking KEMA Keur				
	certificate				
Energy consumption kWh/1,000 hours	17 kWh				
EPREL registration number	1,384,134				
CE mark	Yes				
EU RoHS compliant	Yes				


Product data				
Full EOC	871869674329400			
Order product name	MAS LEDtube HF 1200mm HE 16.5W 830 T5			
Order code	74329400			
SAP numerator – quantity per pack	1			
Numerator – packs per outer box	10			
Material number (12NC)	929001391002			
Net weight	0.160 kg			
Full product name	Master LEDtube HF 1200mm HE 16.5W 830 T5			
EAN/UPC - Case	8718696743300			

# Dimensional drawing



Product	D1	D2	A1	A2	А3
MAS LEDtube HF 1200mm HE	15.5 mm	18.8 mm	1,149 mm	1,156.1 mm	1,163.2 mm
16.5W 830 T5					

#### Photometric data





Light Distribution Diagram - MAS LEDtube HF 1200mm HE 16.5W 830 T5


180°


#### Photometric data




Spectral Power Distribution Colour - MAS LEDtube HF 1200mm HE 16.5W 830 T5

#### Lifetime






Life Expectancy Diagram - MAS LEDtube HF 1200mm HE 16.5W 830 T5




Life Expectancy Diagram - MAS LEDtube HF 1200mm HE 16.5W 830 T5



Lumen Maintenance Diagram - MAS LEDtube HF 1200mm HE 16.5W 830 T5

Life Expectancy Diagram - MAS LEDtube HF 1200mm HE 16.5W 830 T5

#### Lifetime



Lumen Maintenance Diagram - MAS LEDtube HF 1200mm HE 16.5W 830 T5



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.