




# Doppelmaulschlüssel MOTOR

DIN 3110, ISO 10102 (metrische Maße),  
 Chrome-Alloy-Steel, verchromt.



Code		L	b1	b2	a	 g	l
	"	mm	mm	mm	mm		
40431620	1/4 x 5/16	140	16	18	4	21	
40432024	5/16 x 3/8	140	18	23	4,5	34	
40432428	3/8 x 7/16	155	23	26	4,8	48	
40432832	7/16 x 1/2	170	26	30	5,3	58	
40433234	1/2 x 9/16	190	30	32	5,3	73	
40433436	9/16 x 5/8	205	32	36	5,8	96	
40433538	19/32 x 11/16	205	35	40	5,8	105	
40433638	5/8 x 11/16	205	36	40	5,8	101	
40433640	5/8 x 3/4	220	36	42	6,7	135	
40433840	11/16 x 3/4	220	40	42	6,7	135	
40433842	11/16 x 13/16	235	40	47	7,3	167	
40434044	3/4 x 7/8	235	42	49	7,3	177	
40434142	25/32 x 13/16	235	45	47	7,3	190	
40434446	7/8 x 15/16	250	49	53	7,8	235	
40434648	15/16 x 1	270	53	55	8,3	303	
40435258	1 1/8 x 1 5/16	300	64	75	9,4	502	