

Ordering information

Designation	Type	Order No.
Choose your R&S®ScopeRider base models		
Handheld Oscilloscope, 60 MHz, 2 channels, CAT IV, DMM	R&S®RTH1002	1317.5000k02
Handheld Oscilloscope, 60 MHz, 4 channels, CAT IV	R&S®RTH1004	1317.5000k04
Choose your bandwidth upgrade		
Upgrade of R&S®RTH1002 oscilloscopes to 100 MHz bandwidth	R&S®RTH-B221	1325.9717.02
Upgrade of R&S®RTH1002 oscilloscopes to 200 MHz bandwidth	R&S®RTH-B222	1325.9723.02
Upgrade of R&S®RTH1002 oscilloscopes to 350 MHz bandwidth	R&S®RTH-B223	1325.9730.02
Upgrade of R&S®RTH1002 oscilloscopes to 500 MHz bandwidth	R&S®RTH-B224	1326.0571.02
Upgrade of R&S®RTH1004 oscilloscopes to 100 MHz bandwidth	R&S®RTH-B241	1326.0588.02
Upgrade of R&S®RTH1004 oscilloscopes to 200 MHz bandwidth	R&S®RTH-B242	1326.0594.02
Upgrade of R&S®RTH1004 oscilloscopes to 350 MHz bandwidth	R&S®RTH-B243	1326.0607.02
Upgrade of R&S®RTH1004 oscilloscopes to 500 MHz bandwidth	R&S®RTH-B244	1326.0613.02
Choose your options		
Mixed Signal Upgrade for non-MSO models, 250 MHz	R&S®RTH-B1	1325.9981.02
I ² C/SPI Serial Triggering and Decoding	R&S®RTH-K1	1325.9969.02
UART/RS-232/RS-422/RS-485 Serial Triggering and Decoding	R&S®RTH-K2	1325.9975.02
CAN/LIN Serial Triggering and Decoding	R&S®RTH-K3	1333.0550.02
History and Segmented Memory	R&S®RTH-K15	1326.1803.02
Spectrum Analysis	R&S®RTH-K18	1333.0680.02
Advanced Triggering	R&S®RTH-K19	1326.0642.02
Frequency Counter	R&S®RTH-K33	1333.0696.02
Harmonics Analysis	R&S®RTH-K34	1333.0673.02
Wireless LAN, all countries except US and Canada	R&S®RTH-K200	1326.0620.02
Wireless LAN, for US and Canada only	R&S®RTH-K200US	1332.9890.02
Web Interface Remote Control	R&S®RTH-K201	1326.0636.02
Choose your probes		
Passive Probe, 500 MHz, isolated, 10:1, 10 M Ω , 12 pF, 600 V CAT IV, 1000 V CAT III	R&S®RT-ZI10	1326.1761.02
Passive Probe, 500 MHz, isolated, 100:1, 100 M Ω , 4.6 pF, 600 V CAT IV, 1000 V CAT III, (3540 V CAT I)	R&S®RT-ZI11	1326.1810.02
Passive Probe (laboratory model), 500 MHz, isolated, 10:1, 10 M Ω , 11 pF, 300 V CAT III	R&S®RT-ZI10C	1326.3106.02
Set 2 x R&S®RT-ZI10C passive probe	R&S®RT-ZI10C-2	1333.1811.02
Set 4 x R&S®RT-ZI10C passive probe	R&S®RT-ZI10C-4	1333.1328.02
20 kHz, AC/DC, 0.01 V/A and 0.001 V/A, \pm 200 A and \pm 2000 A	R&S®RT-ZC02	1333.0850.02
100 kHz, AC/DC, 0.1 V/A, 30 A	R&S®RT-ZC03	1333.0844.02
Accessory Replacement Set for R&S®RT-ZI10/R&S®RT-ZI11	R&S®RT-ZA20	1326.1978.02
Accessory Extension Set for R&S®RT-ZI10/R&S®RT-ZI11	R&S®RT-ZA21	1326.1984.02
Safety Test Leads, red and black, silicone, 600 V CAT IV	R&S®RT-ZA22	1326.0988.02
PT100 Temperature Probe	R&S®RT-ZA12	1333.0809.02
Choose your accessories		
Soft Carrying Bag	R&S®HA-Z220	1309.6175.00
Ethernet Cable, length: 2 m, crossover	R&S®HA-Z210	1309.6152.00
USB Cable, length: 1.8 m, standard/mini USB connector	R&S®HA-Z211	1309.6169.00
Hard Shell Protective Carrying Case	R&S®RTH-Z4	1326.2774.02
Car Adapter	R&S®HA-Z302	1321.1340.02
Battery Charger for Lithium-Ion Battery	R&S®HA-Z303	1321.1328.02
Replacement Battery	R&S®HA-Z306	1321.1334.02
Spare Power Supply for R&S®RTH incl. power plugs for EU, GB, US	R&S®RT-ZA14	1326.2874.02