

DIN 653

Rändelschrauben, niedrige Form



Maße	M 3	M 4	M 5	M 6	M 8	M 10
$\varnothing d_k$	12	16	20	24	30	36
k_{max}	2,5	3,5	4	5	6	8
$\varnothing d_s$	3	4	5	6	8	10
e	2	3	3	4	5	6