




KS 8.10 FL40 STTZN (321 045)



Figure without obligation



Type	KS 8.10 FL40 STTZN
Part No.	321 045
Material of clamp	St/tZn
Clamping range Rd / FI	8-10 / 30-40 mm
Clamping range FI / FI	30-40 / 30-40 mm
Screw	☛ M8 x 30 mm
Material of screw / nut	St/tZn
Dimension	70 x 70 x 3 mm
Intermediate plate	yes
Standard	EN 62561-1
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	12.6 kA
Zinc coating acc. EN 1461	≥ 70 μm
Weight	413 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364021518
PU	25 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.