


# Sheets and accessories



## Stretch sheets

Color	Thickness	Dim. a	Dim. b	Packaging	Min.OU	Width	Length	EAN / item no.
<b>1 Stretch metal in raw steel</b>								
raw	1.2 mm	6.0 mm	3.5 mm	sealed	5 pcs.	250 mm	500 mm	4001116 <b>37604</b> 7
raw	1.2 mm	6.0 mm	3.5 mm	sealed	5 pcs.	120 mm	1000 mm	4001116 <b>37600</b> 9
raw	1.2 mm	6.0 mm	3.5 mm	sealed	5 pcs.	200 mm	1000 mm	4001116 <b>37601</b> 6
raw	1.2 mm	6.0 mm	3.5 mm	sealed	5 pcs.	300 mm	1000 mm	4001116 <b>37602</b> 3
raw	1.2 mm	6.0 mm	3.5 mm	sealed	5 pcs.	600 mm	1000 mm	4001116 <b>37603</b> 0
raw	2.2 mm	10.0 mm	5.8 mm	sealed	5 pcs.	600 mm	1000 mm	4001116 <b>37653</b> 5
raw	2.2 mm	10.0 mm	5.8 mm	sealed	5 pcs.	120 mm	1000 mm	4001116 <b>37650</b> 4
raw	2.2 mm	10.0 mm	5.8 mm	sealed	5 pcs.	200 mm	1000 mm	4001116 <b>37651</b> 1
raw	2.2 mm	10.0 mm	5.8 mm	sealed	5 pcs.	300 mm	1000 mm	4001116 <b>37652</b> 8
raw	2.2 mm	10.0 mm	5.8 mm	sealed	5 pcs.	250 mm	500 mm	4001116 <b>37654</b> 2
raw	2.8 mm	16.0 mm	8.0 mm	sealed	5 pcs.	250 mm	500 mm	4001116 <b>37704</b> 4
raw	2.8 mm	16.0 mm	8.0 mm	sealed	5 pcs.	120 mm	1000 mm	4001116 <b>37700</b> 6
raw	2.8 mm	16.0 mm	8.0 mm	sealed	5 pcs.	200 mm	1000 mm	4001116 <b>37701</b> 3
raw	2.8 mm	16.0 mm	8.0 mm	sealed	5 pcs.	300 mm	1000 mm	4001116 <b>37702</b> 0
raw	2.8 mm	16.0 mm	8.0 mm	sealed	5 pcs.	600 mm	1000 mm	4001116 <b>37703</b> 7