

Pre-Crimped Leads

Molex's range of pre-crimped leads offers a simple, cost-effective solution for prototyping, pre-production and mass production requirements. These leads are offered in female-to-female and male-to-male configurations in lengths of 75.00 to 600.00mm

Features and Advantages

| Pre-crimped and fully tested cables | Decrease time to market |
|---|---|
| Available in 75.00 to 600.00mm lengths | Works well for all prototype and pre-production requirements |
| Leads crimped on both ends | Allows for wire-to-wire applications and when cut in half, wire-to-board applications |
| UL listed cables | Assures high-quality approved materials |
| Available for most popular Molex families | Helps customers choose the right connector before investing in application tooling |























































Sherlock Sabre

SL

Ultra-Fit





Ordering Information

| Product Family | Series Number | Length (mm) | Connector A | Connector B | Wire Size (AWG) | Wire/Cable Type |
|-----------------|---|------------------------|--------------|-----------------|-------------------|-------------------|
| C-Grid | 79758 | 150, 300 | Female | Female | 22 | UL 1061 |
| CLIK-Mate | 79758, 215710, 215711 | 75, 150, 225, 300, 450 | Female, Male | Female, Male, - | 24, 26, 28 | UL 1061, UL 10002 |
| DuraClik | 79758 | 150, 300 | Female | Female | 26 | UL 1061 |
| KK | 79758 | 150, 300 | Female, Male | Female, Male | 22, 24 | UL 1061, UL 1007 |
| L1NK 396 | 79758 | 150 | Female | Female | 18 | UL 1051 |
| Mega-Fit | 79758 | 150, 300 | Female | Female | 16, 12 | UL 1015 |
| Micro-Clasp | 79758 | 150, 300 | Female | Female | 24 | UL 1007 |
| Micro-Fit 3.0 | 79758, 214760, 214761, 214762, 214763 | 150, 300, 600 | Female, Male | Female, Male, - | 18, 20 | UL 1061, UL10002 |
| Micro-Lock Plus | 79758 | 150, 300 | Female | Female | 26 | UL 1061 |
| Milli-Grid | 79758 | 150, 300 | Female | Female | 24 | UL 1061 |
| Mini-Fit | 79758, 215340, 215341, 215342, 215343 | 75, 150, 225, 300, 450 | Female, Male | Female, Male | 16, 18, 20 | UL 1015, UL 1061 |
| Mini-Lock | 79758 | 150, 300 | Female | Female | 22 | UL 1061 |
| MLX | 79758 | 150, 300 | Female, Male | Female, Male | 18 | UL 1015 |
| Multicat | 79758 | 150, 300 | Female, Male | Female, Male | 8, 9, 12, 16 | UL 1199 |
| Nano-Fit | 79758 | 150, 300 | Female | Female | 20 | UL 1061 |
| PicoBlade | 79758, 214920, 214921, 214922, 214923 | 75, 150, 225, 300, 450 | Female, Male | Female, Male, - | 26, 28, 26 and 28 | UL1061 |
| Pico-Clasp | 79758 | 150, 300 | Female | Female | 28 | UL 1571 |
| Pico-EZmate | 79758 | 300 | Female | Female | 28 | UL 1516 |





Ordering Information

| Product Family | Series Number | Length (mm) | Connector A | Connector B | Wire Size (AWG) | Wire/Cable Type |
|----------------|---------------|-------------|--------------|--------------|-----------------|------------------|
| Pico-Lock | 79758 | 150, 300 | Female | Female | 24, 30 | UL 1061, UL 1571 |
| Pico-SPOX | 79758 | 150, 300 | Female | Female | 24 | UL 1061 |
| Sabre | 79758 | 150, 300 | Female, Male | Female, Male | 16 | UL 1015 |
| Sherlock | 79758 | 150, 300 | Female | Female | 26 | UL 1061 |
| SL | 79758 | 150 | Female | Female | 22 | UL 1061 |
| Standard .062" | 79758 | 150, 300 | Female, Male | Female, Male | 22 | UL 1015 |
| Standard .093" | 79758 | 150, 300 | Female, Male | Female, Male | 18 | UL 1015 |
| Ultra-Fit | 79758 | 150, 300 | Female | Female | 16 | UL 1061 |

Order No. 987651-2631 Rev. 5 USA/0k/GF/2020.08 ©2020 Molex