



HEAT SHRINK TUBING



Thomas & Betts
A Member of the ABB Group

PKGB 3:1, WITH ADHESIVE BOX

Applications:	Heat shrink tubing with adhesive liner
Material:	Polyolefin
Temperature range:	-55°C to +110°C
Lowest shrink temperature:	+95°C
Wall thickness:	Thin wall, double wall with adhesive liner
Shrink ratio:	3:1
Self-extinguishing:	Yes

Product Description	Nelco Stock code
SHRINK HOSE WITH ADHESIVE, 3:1, ID = 3.0 MM BLACK, BOX, L = 5.0 M, THIN WALL	PKGB 3-1
SHRINK HOSE WITH ADHESIVE, 3:1, ID = 6.0 mm BLACK, BOX, L = 3.5 m, THIN WALL	PKGB 6-2
SHRINK HOSE WITH ADHESIVE, 3:1, ID = 9.0 mm BLACK, BOX, L = 3.0 m, THIN WALL	PKGB 9-3
SHRINK HOSE WITH ADHESIVE, 3:1, ID = 12.0 mm BLACK, BOX, L = 2.5 m, THIN WALL	PKGB 12-4
SHRINK HOSE WITH ADHESIVE, 3:1, ID = 18.0 mm BLACK, BOX, L = 2.0 m, THIN WALL	PKGB 18-6
SHRINK HOSE WITH ADHESIVE, 3:1, ID = 24.0 mm BLACK, BOX, L = 1.5 m, THIN WALL	PKGB 24-8

NELCO CONTACT AB

Daléns gata 7, 195 61 Arlandastad, Sweden - +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se