

Crimp Fittings

Press-armaturen


Embouts sertis

Raccordi a graffare

Racores para presión

KS


Komatsu Split Flange
Komatsu Flansch
Bride Komatsu
Flangia Komatsu
Brida Komatsu



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
	1S10KS10	1A10KS10					-10	94,8	65,4		11,7			34,2
	1S12KS12						-12	109,4	79,2		15,5			38,1
	1S16KS16	1A16KS16					-16	116,0	81,6		20,7			44,5
	1S20KS20						-20	118,2	74,2		26,6			50,8
	1S24KS24	1A24KS24					-24	144,0	98,2		32,0			60,3
	1S32KS32						-32	183,0	130,8		44,4			71,4

KSA

Komatsu Split Flange, 45° Elbow
Komatsu Flansch, 45° Krümmer
Bride Komatsu, coudé 45°
Flangia Komatsu a 45°
Brida Komatsu acodado a 45°



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
	1S10KSA10	1A10KSA10					-10	76,7	47,3	21,9	11,7			34,2
	1S12KSA12						-12	111,5	81,3	26,0	15,5			38,1
	1S16KSA16	1A16KSA16					-16	115,9	81,5	28,3	20,7			44,5
	1S20KSA20						-20	150,9	106,9	36,4	26,6			50,8
	1S24KSA24						-24	145,0	98,7	32,0	32,0			60,3
	1S32KSA32						-32	178,2	126,0	58,8	44,4			71,4