

Crimp Fittings

Press-armaturen


Embouts sertis

Raccordi a graffare

Racores para presión

FRA


ORS Female Swivel, 45° Elbow
 ORS-Anschluss, 45° Krümmer
 Femelle ORS coudé 45°
 Femmina ORS a 45°
 Hembra loca ORS acodado a 45°



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G4FRA4	1S4FRA4	1A4FRA4	9/16-18				-4	53,0	29,6	10,4	4,2	17		
1G6FRA5	1S6FRA5	1A6FRA5	11/16-16				-5	58,3	34,4	10,9	5,3	22		
1G6FRA6	1S6FRA6	1A6FRA6	11/16-16				-6	59,7	34,4	10,9	6,2	22		
1G8FRA6	1S8FRA6	1A8FRA6	13/16-16				-6	67,2	41,9	15,0	6,7	24		
1G8FRA8	1S8FRA8	1A8FRA8	13/16-16				-8	72,1	43,1	15,0	9,4	24		
1G10FRA10	1S10FRA10	1A10FRA10	1-14				-10	76,2	47,8	16,5	11,7	30		
1G12FRA12	1S12FRA12	1A12FRA12	1 3/16-12				-12	88,6	58,4	21,1	14,8	36		
1G16FRA16	1S16FRA16	1A16FRA16	1 7/16-12				-16	107,6	73,2	23,9	19,3	41		
1G20FRA20	1S20FRA20	1AP20FRA20*	1 11/16-12				-20	129,6	85,6	25,4	25,7	50		
		1AT20FRA20**	1 11/16-12				-20	129,6	85,6	25,4	25,7	50		
1G24FRA24	1S24FRA24	1A24FRA24	2-12				-24	115,2	68,9	27,3	32,0	60		

FRB

ORS Female Swivel, 90° Elbow
 ORS-Anschluss, 90° Krümmer
 Femelle ORS coudé 90°
 Femmina ORS a 90°
 Hembra loca ORS acodado a 90°



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G4FRB4	1S4FRB4	1A4FRB4	9/16-18				-4	53,0	29,6	20,8	4,2	17		
1G6FRB4	1S6FRB4	1A6FRB4	11/16-16				-4	56,3	32,9	22,9	4,2	22		
1G6FRB5	1S6FRB5	1A6FRB5	11/16-16				-5	56,9	33,0	22,9	5,3	22		
1G6FRB6	1S6FRB6	1A6FRB6	11/16-16				-6	59,4	34,1	22,9	6,7	22		
1G8FRB6	1S8FRB6	1A8FRB6	13/16-16				-6	66,5	41,2	29,2	6,7	24		
1G8FRB8	1S8FRB8	1A8FRB8	13/16-16				-8	72,1	42,4	29,2	9,4	24		
1G10FRB10	1S10FRB10	1A10FRB10	1-14				-10	78,0	48,6	32,3	11,5	30		
1G12FRB12	1S12FRB12	1A12FRB12	1 3/16-12				-12	88,7	58,5	47,8	14,8	36		
1G16FRB16	1S16FRB16	1A16FRB16	1 7/16-12				-16	107,3	72,9	56,1	19,9	41		
1G20FRB20	1S20FRB20	1AP20FRB20*	1 11/16-12				-20	134,6	90,6	63,8	25,7	50		
		1AT20FRB20**	1 11/16-12				-20	134,6	90,6	63,8	25,7	50		
1G24FRB24	1S24FRB24	1A24FRB24	2-12				-24	117,8	71,5	68,6	32,0	60		

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

Specification subject to change without notice