



Main

Range	TeSys
Device short name	VZ
Product or Component Type	Additional pole
Performance level	High performance
Poles description	1P
Contacts type and composition	1 NO
Product Compatibility	V2
Range compatibility	TeSys (TeSys VARIO) switch disconnecter
Network type	AC DC
Network Frequency	50/60 Hz
Suitability for isolation	Yes

Complementary

Mounting Location	Right Left
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	40 A
[Ithe] conventional enclosed thermal current	32 A
Mechanical durability	100000 cycles
Electrical durability	100000 Cycles AC-21 30000 cycles DC-1...5
Connections - terminals	Power circuit screw clamp terminals 0.01 in ² (6 mm ²) flexible - with cable end Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid
Tightening torque	Power circuit 18.59 lbf.in (2.1 N.m) screw clamp terminals
Height	2.91 in (74 mm)
Width	0.63 in (16 mm)
Depth	1.38 in (35 mm)
Net Weight	0.11 lb(US) (0.05 kg)

Environment

Standards	IEC 60947-3
Product Certifications	CSA GL UL UKCA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21730-V VARIO SWITCH
Discount Schedule	CP1
GTIN	3389110551877
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.46 in (3.7 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	1.66 oz (47.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	69
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.93 lb(US) (3.599 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------