



**Round connector M16 x 0.75  
male, straight, customizable  
BS6-0**



- Solder connection
- 6-pin
- PG9 screw-in thread
- Cable feedthrough 6.0...8.0 mm

**Pin Assignment**



<b>Type designation</b>	BS6-0
Ident no.	6934732
<b>Connector A side</b>	
Number of pins	Field-wireable connector, M16 $\leftarrow$ 0.75, Straight 6
Contacts	Bronze, CuSn, Silver-plated
Contact carriers	Plastic, PBT UL94-V0, Black
Grip	Plastic, PA, Black
Coupling nut/screw	Die-cast zinc, GD-Zn, Nickel-plated
Screw-in thread	PG9
External diameter of the cable	min. 6...8mm
Core cross-section/Clamping ability	0.14...0.75mm <sup>2</sup>
Connection mode	Solder contact
Mechanical lifespan	> 500 Mating cycles
Pollution degree	1
Protection class	IP67, (screwed together)
<b>Electrical features at +20 °C</b>	
Rated voltage	60 V
Current	5 A
Insulation resistance	$\geq 10^8 \Omega$
Forward resistance	$\leq 5 \text{ m}\Omega$
<b>Mechanical and chemical properties</b>	
Ambient temperature	
Stationary	-40...+95°C