

CTM110C2



Article Number: 151-30404

Cable Tie Mount, 0.19" Hole Dia., 0.2" Max Tie Width, PA66, White, 100/pkg

 RoHS

 Download spec sheet

Base Data

Local Order Number	CTM110C2
Type	CTM1
Color	White (WH)
Features and Benefits	• Designed for use with 18 through 50 pound cable ties to provide stability when securing bundles. • Secures with a single screw providing quick installation.
Product Description	HellermannTyton cable tie mounts are designed for use with 18 through 120 pound cable ties to provide stability when securing bundles. The mounts are installed quick and easy by securing a single screw.
Short Description	Cable Tie Mount, 0.19" Hole Dia., 0.2" Max Tie Width, PA66, White, 100/pkg

Product Dimensions

Length L (Imperial)	0.58 "
Length L (Metric)	14.7 mm
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.37 "
Width W (Metric)	9.4 mm
Cable Tie Width Max. (Imperial)	0.2 "
Cable Tie Width Max. (Metric)	5.0 mm
Height H (Imperial)	0.27 "
Height H (Metric)	6.9 mm
Mounting Hole Diameter D (Imperial)	0.19 "
Mounting Hole Diameter D (Metric)	4.8 mm
Mounting Hole Diameter D Max. (Metric)	4.8 mm
Mounting Hole Diameter D Min. (Metric)	4.8 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100 Pieces
Carton Quantity	10000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

Certification/Specification UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes