

Product information

12 42 195

KNIPEX MultiStrip 10 Automatic Insulation Stripper




- Stripping without re-adjustment from 0.03 to 10.0 mm²
- Recessed wire cutter
- Universal blade geometry – robust and more durable
- Ideal grip design with excellent haptics
- Fully automatic adjustment to fine-stranded conductors with standard insulation throughout the entire capacity range from 0.03 to 10.0 mm²
- With recessed wire cutter for Cu and Al conductors, stranded up to 10 mm² and single wire up to 6 mm²
- No damage to the conductors
- The clamping jaws made of steel hold the cable in a way that prevents slipping without damaging the remaining insulation
- Particularly smooth-running mechanics and very low weight
- Replaceable blades block and length stop
- Handle with soft-plastic zone for a steady grip
- Body: glass fibre reinforced plastic
- Blade: special tool steel, oil-hardened

AAA



General	
Article No.	12 42 195
EAN	4003773054580
Weight	136 g
Dimensions	195 x 112 x 18 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable
Technical details	
Stripping capacities in square millimetres	0.03 — 10.0 mm ²
AWG	32 — 8

technical change and errors excepted



Wire cutter for multiple stranded wire cables up to 10.0 mm²