



### Main

|              |                                    |
|--------------|------------------------------------|
| Product line | QO                                 |
| Product type | Load Center Grounding Bar Assembly |

### Complementary

|                           |   |
|---------------------------|---|
| Number of connectors      | 12  |
| Wire size                 | AWG 14...AWG 4 copper<br>AWG 12...AWG 4 aluminium   |
| Provided equipment        | 2 screw   |
| Bar length                | 4.69 in (119 mm)  |
| Maximum length of segment | 3.15 in (80 mm)   |
| Device mounting           | Direct mounting back of enclosure   |
| Tightening torque         | 30 lb.in<br>Mounting screw 30 lb.in<br>20 lb.in, AWG 14...AWG 10, copper<br>20 lb.in, AWG 12...AWG 10, aluminium<br>35 lb.in, AWG 6...AWG 4<br>25 lb.in, AWG 8<br>25 lb.in, AWG 14...AWG 12, copper<br>25 lb.in, AWG 12...AWG 10, aluminium |

### Ordering and shipping details

|                     |                           |
|---------------------|---------------------------|
| Category            | 00102 - QO LC ACCESSORIES |
| Discount Schedule   | DE3A                      |
| GTIN                | 00785901026402            |
| Package weight(Lbs) | 0.2 lb(US) (0.09 kg)      |
| Returnability       | Yes                       |
| Country of origin   | US                        |

### Packing Units

|                  |                            |
|------------------|----------------------------|
| Package 2 Weight | 329.00 lb(US) (149.232 kg) |
|------------------|----------------------------|

### Offer Sustainability

|                           |  |
|---------------------------|--|
| California proposition 65 | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation          | REACH Declaration  |
| REACH free of SVHC        | Yes  |
| EU RoHS Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration                            |
| Toxic heavy metal free    | Yes  |
| Mercury free              | Yes  |

---

|                            |  |
|----------------------------|--|
| RoHS exemption information | <a href="#">Yes</a>                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a> |

---

### Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---