

## Electronic pocket vernier callipers

TWIN-CAL IP67



### Application:

For measuring external, internal, step and depth dimensions.

### Execution:

- With locking screw
- ON
- mm/inch changeover
- AUTO OFF
- Zero setting at any position
- ABS function

### Advantage:

- Long operating time of over 12,000 hours
- Soft Touch for comfortable handling
- IP protection, even with a data transfer cable connected

### Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032)



<b>Art. no.</b>	<b>31174 210</b>
<b>Brand</b>	TESA
<b>Manufacturer Part Number</b>	00530322
<b>Min./max. length measuring range</b>	0-200 mm
<b>Data transmission type</b>	TLC
<b>Depth gauge rod</b>	Flat
<b>IP protection class</b>	IP 67
<b>With drive wheel</b>	Yes
<b>Length of jaw</b>	50 mm
<b>Digit height</b>	11 mm
<b>Length of cross tips</b>	20 mm
<b>Digit increment</b>	0.01 mm
<b>Digit increment in inches</b>	0.0005 in
<b>Type of locating</b>	With locking screw
<b>Battery designation</b>	3V CR2032 Lithium
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Weight of rechargeable battery/battery</b>	0.003 kg
<b>Battery voltage</b>	3 V
<b>Type of rechargeable battery/battery</b>	Lithium
<b>Calibration Group</b>	A
<b>ISO</b>	13385-1
<b>Type</b>	TWIN-CAL IP67
<b>Gross Weight</b>	0.472 kg
<b>Product Group</b>	362

### EAN

7630041106312

