

Electronic inclinometer

CLINOBEVEL 1 USB in set



Application:

For fast and easy measurement of inclines using absolute and comparative measuring procedures

Version:

- 4 precisely machined measuring bases
- Splash-proof housing (IP65)
- USB interface
- Selectable units of measure: Degrees (2 dec.), degrees/min., mm/m (2 dec.), inch/10 or 12 inch (4 dec.), mm or inch/rel. basis (optional), milliradians and others
- Battery operation
- Measuring range +/- 45°
- Error limit: 2' + 1 digit increment
- Digit increments: 0.02 mm/m
- Includes USB data cable and software

Delivery:

Inclinometer incl. Battery (1x1.5 V type AA), USB data cable, Clinisoft software, in a case



Art. no.	38448 011
Length x width x height	100 x 35 x 75 mm
Type	TESA CLINOBEVEL 1 USB
Device dimensions	100 x 35 x 75 mm

EAN-Code

7630041115321