

## Round sling with long service life

The all-rounder for everyday use

### Execution:

- Additionally labelled with load capacity and marked with woven-in barrel strips
- Tear-proof, double label sewn in
- Complies with EN 1492-2
- GS-tested
- Can be used between -40°C and +100°C

### Advantage:

- low tare weight
- Versatile

### Delivery:

Includes operating instructions and declaration of conformity



<b>Art. no.</b>	<b>77199 410</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	77199410
<b>Length</b>	1000 mm
<b>Load-bearing capacity (single direct)</b>	4000 kg
<b>Load-bearing capacity (single u-shape)</b>	8000 kg
<b>Load-bearing capacity (single noosed)</b>	3200 kg
<b>Width of support plate under load</b>	65 mm
<b>Thickness of support plate under load</b>	8 mm
<b>Material</b>	PES - Polyester
<b>Colour</b>	Grey
<b>Approval mark</b>	GS - TÜV Rheinland
<b>Gross Weight</b>	0.840 kg
<b>Product Group</b>	7EJ

### EAN

4053625461875