

Item no.: 3089724

Data Sheet

USB to RS232 DB9, FTDI-Chip




- Data Rate: 3M Baud
- Interface: UART
- End connector: DB9
- Cable details: UL2464 28AWG 9C, 5.5 mm
- Channel: 1
- USB Class: FTDI Drivers
- Max power output: RS232 + -12 V
- ESD: 4 kV
- Operating temperature: -10 – 55 °C
- USB speed: Full speed
- USB Connector: Type CM
- Cable length: 1 m
- I/O voltage: 5 V
- Virtual Com port: yes
- FTDI internal IC: RT232RL

Item no.: 3089724

Data Sheet

RoHS



1000±20mm

USB AM(Nickel plated)
Black molding, NO:2161
TOL:±0.5mm

DB 9F(Nickel plated)
Black molding
TOL:±0.5mm

PCB: KA-892 REV1.0(C: FT232RL+UM213)

PIN ASSIGNMENT:

PCB	DB 9F
DCD	1 BLACK
TXD	2 BROWN
RXD	3 RED
DSR	4 ORANGE
GND	5 YELLOW
DTR	6 GREEN
CTS	7 BLUE
RTS	8 PURPLE
RI	9 GREY
AM SHELL	Drain SHELL

No.	Description	Qty
①	UL2464 28#*9Q(black, brown, red, orange, yellow, green, blue, purple, grey)+F+AL+D(70127TC)+R(16*8010TC)+OD-5.5mm Black PVC Jacket	1PCS
②	USB AM(White Insulator, Nickel Plated)	1PCS
③	DB 9F(Black Insulator, Nickel Plated)	1PCS
④	Black 45P PVC	10g
⑤	PE	5g
⑥	SCREW	2PCS
⑦	PCB: KA-892 REV1.0(C: FT232RL+UM213)	1PCS