



### Main

Range of product	OsiSense XG
Product or component type	Electronic tag
RFID electronic tag name	XGSZ
RFID frequency	13.56 MHz
Design	ISO badge
Associated smart antenna	XGCS491
Outer dimension	54 x 85.5 x 1 mm
Quantity per set	Set of 1
IP degree of protection	IP65

### Complementary

Memory type	EEPROM
Memory operation	Read
Number of read cycles	Unlimited
Number of write cycles	- -13...122 °F (-25...50 °C)
Data retention time	10 year(s)
Material	PVC (polyvinyl chloride)
Net Weight	0.07 lb(US) (0.03 kg)

### Environment

Standards	ISO 14443
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...131 °F (-40...55 °C)

### Ordering and shipping details

Category	22491 - SENS,IDENTIFICATION DEVICE (XGK)
Discount Schedule	DS2
GTIN	00785901963318
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1 lb(US) (0.05 kg)
Returnability	No
Country of origin	MY

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.59 in (1.5 cm)
Package 1 width	3.35 in (8.5 cm)
Package 1 Length	4.33 in (11 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>