

Electronics Super Knips ESD

Straight head, burnished, without chamfer, with wire clamp



Application:

For precision cutting tasks in electronics and precision mechanics fields.

Execution:

- Special tool steel, burnished
- Ground, very sharp blades without chamfer for flush cutting
- Joint with stainless steel rivet
- With opening spring and opening limiter

Advantage:

- Safe, ergonomic and fatigue-free working thanks to two-component handles
- Precisely shaped tips also cut close-fitting wires from a diameter of 0.2 mm
- Extremely smooth action for fatigue-free working
- With wire clamp – no uncontrolled displacement of wire sections
- ESD design, discharges electricity



Art. no.	53107 080
Brand	KNIPEX
Manufacturer Part Number	78 71 125 ESD
Length	125 mm
Max. soft wire diameter cutting capacity	1.6 mm
Head design	Without bevel, With wire clamp, burnished
Surface	Burnished
Material of handle	2-component plastic
ESD-capable	Yes
Gross Weight	0.059 kg
Product Group	535

EAN

400377302519 1