




## Türschloss M-TS PT mit 2 MF-HO E92 Stulp 24/16

### Technische Zeichnung



|     |        |    |    |   |       |               |       | L     |   | No                     |
|-----|--------|----|----|---|-------|---------------|-------|-------|---|------------------------|
| fix | silber | 92 | 35 | 8 | 1.050 | 2.000 - 2.200 | 24/16 | 2.200 | 1 | <a href="#">245530</a> |
|     |        |    | 40 | 8 | 1.050 | 2.000 - 2.200 | 24/16 | 2.200 | 1 | <a href="#">245531</a> |
|     |        |    | 45 | 8 | 1.050 | 2.000 - 2.200 | 24/16 | 2.200 | 1 | <a href="#">245532</a> |
|     |        |    | 50 | 8 | 1.050 | 2.000 - 2.200 | 24/16 | 2.200 | 1 | <a href="#">245533</a> |
|     |        |    | 55 | 8 | 1.050 | 2.000 - 2.200 | 24/16 | 2.200 | 1 | <a href="#">245534</a> |
|     |        |    | 65 | 8 | 1.050 | 2.000 - 2.200 | 24/16 | 2.200 | 1 | <a href="#">245536</a> |
|     |        |    | 80 | 8 | 1.050 | 2.000 - 2.200 | 24/16 | 2.200 | 1 | <a href="#">245538</a> |

### Schraubpositionstabelle

| No                     |    |        |      |      |        |        |      |       |     |     |     |     |       |
|------------------------|----|--------|------|------|--------|--------|------|-------|-----|-----|-----|-----|-------|
| <a href="#">245530</a> | 12 | -1.000 | -870 | -650 | -585,6 | -466,9 | -304 | 143,5 | 265 | 620 | 840 | 970 | 1.100 |
| <a href="#">245531</a> | 12 | -1.000 | -870 | -650 | -585,6 | -466,9 | -304 | 143,5 | 265 | 620 | 840 | 970 | 1.100 |
| <a href="#">245532</a> | 12 | -1.000 | -870 | -650 | -585,6 | -466,9 | -304 | 143,5 | 265 | 620 | 840 | 970 | 1.100 |
| <a href="#">245533</a> | 12 | -1.000 | -870 | -650 | -585,6 | -466,9 | -304 | 143,5 | 265 | 620 | 840 | 970 | 1.100 |
| <a href="#">245534</a> | 12 | -1.000 | -870 | -650 | -585,6 | -466,9 | -304 | 143,5 | 265 | 620 | 840 | 970 | 1.100 |
| <a href="#">245536</a> | 12 | -1.000 | -870 | -650 | -585,6 | -466,9 | -304 | 143,5 | 265 | 620 | 840 | 970 | 1.100 |
| <a href="#">245538</a> | 12 | -1.000 | -870 | -650 | -585,6 | -466,9 | -304 | 143,5 | 265 | 620 | 840 | 970 | 1.100 |