

# AC-DC Switching Adapter

## 17.5 W, Euro plug



### FEATURES:

With over voltage, over current and over power protection

L.P.S (Limits for power source)

### SPECIFICATION:

Output voltage	5 VDC
Power	17.5 W
Connection, primary side	Euro plug
Connection, secondary side	2.1 x 5.5 x 12 mm Barrel plug
Input voltage	100...240 VAC
MTBF	50 000 Hours min
Output current	0...3.5 A
Cable length	1.5 m
Dimensions L x W x H	51 x 32 x 87.9 mm
Input frequency	50...60 Hz
No load power consumption	< 0.3 W
Line regulation	0.5 %
Operating temperature max.	35 °C
Operating temperature min.	0 °C
Short-circuit-proof	Yes
Weight	275 g
Appliance	Class II
Efficiency	Efficiency level V



Art. Nr.

**RND 320-00020**

For more information and technical drawings, please contact us at [info@distrelec.com](mailto:info@distrelec.com).

