

ABS 21/18-3



Sample image

Order symbol : ABS 21/18-3

EAN : 6418074056788

Product nr : 7585154


El. number :

Description : Enclosure, ABS

- Finland : 3438243
- Denmark : 8212016761
- Sweden : 7585154

Remarks : Smoked transparent hinged cover

Including : Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices, FC version: Closed PC frame front plate with PUR gasket and cover screws.



Dimensions :	Height	Width	Depth
mm :	235	185	119
inch :	9.25	7.28	4.69

Materials :

Material : ABS
Gasket material : Polyurethane

Accessories :

- FP 21/18 Front plate (aluminium), for enclosures: (207 x 119 x 1)
- FC PC 21/18 Frame of PC front plate, for enclosures: (213 x 125 x 20)
- MP 21/18 Mounting plate, for enclosures: (142 x 200 x 1)

Ratings :

Temperatures :

Temperature °C (continuous) :	-40 ... 60
Temperature °F (continuous) :	-40 ... 140

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK07;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C :	650C

Certificates :

SGSFIMKO_CARDpc