


E10013



Wirable socket

SDOAJ040PLSFKPG



| Electrical data | | |
|-------------------------|------|-------------------|
| Operating voltage | [V] | < 45 AC / < 70 DC |
| Max. current load total | [A] | 4; (...40 °C) |
| Operating conditions | | |
| Ambient temperature | [°C] | -40...85 |
| Protection | | IP 65 |
| Mechanical data | | |
| Weight | [g] | 31.4 |
| Dimensions | [mm] | 43 x 25 x 36 |
| Materials | | PA |
| Material nut | | PA |
| Remarks | | |
| Pack quantity | | 1 pcs. |

Electrical connection
terminals: ...0.75 mm²; Cable sheath: Ø 6...8 mm

Electrical connection - socket
Connector: 1 x M18, angled; Moulded body: PA; Locking: PA



E10013

Wirable socket

SDOAJ040PLSFKPG



Connection

