

## M12 Y-DISTRIBUTOR / M12 FEMALE 90°

PUR 3X0.34 black UL/CSA + ROBOT, drag ch 0.3m

Male straight, to females 90°


Y-connector M12 - M12, 4-pole

Art.-No. 7005 - M12 Lite - (plastic hexagonal screw) on request

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request. Further cable lengths on request.


### [Link to Product](#)

#### Illustration



Y-Male

Females





Product may differ from Image

### Approvals



\* only for products with UL/CSA approved cable

### Form

40741

### Technical Data

|                               |   |
|-------------------------------|---|
| Operating voltage             | max. 250 V AC/DC  |
| Operating current per contact | max. 4 A  |
| Locking of ports              | Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing |
| Protection                    | IP67 inserted and tightened (EN 60529)                            |

### Cables

|                             |                                  |
|-----------------------------|----------------------------------|
| Cable number                | 653                              |
| No./diameter of wires       | 3 × 0.34 mm <sup>2</sup>         |
| Wire isolation              | PP (br, bl, bk)                  |
| C-track properties          | 10 Mio.                          |
| Torsion                     | 1 Mio. ± 360°/m                  |
| Jacket Color                | black                            |
| Shore hardness outer jacket | 58 ± 3D                          |
| Material (jacket)           | PUR (UL/CSA), welding spark res. |
| Outer diameter              | approx. 4.3 mm                   |

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

|                            |              |
|----------------------------|--------------|
| Bend radius (fixed)        | 5 × outer Ø  |
| Bend radius (moving)       | 10 × outer Ø |
| Temperature range (fixed)  | -40...+90 °C |
| Temperature range (mobile) | -25...+90 °C |

**General data**

|                   |  |
|-------------------|--|
| Temperature range | -25...+85 °C, depending on cable quality |
|-------------------|--|

**Commercial data**

|                        |          |
|------------------------|----------|
| country of origin      | DE       |
| customs tariff number  | 85444290 |
| minimum order quantity | 1        |