

Product information


48 21 J11

Precision Circlip Pliers

For internal circlips in bore holes

DIN 5256 D

- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- Angled tips
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



General

Article No.	48 21 J11
EAN	4003773048633
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	105 g
Dimensions	130 x 52 x 12 mm
Standard	DIN 5256 D
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Size of bore	Ø 12 – 25 mm
Tips (diameter)	Ø 1.3 mm

technical change and errors excepted