

Neon Indicators

(Neon, LED and Filament Lamps) - Page 1 of 5



Colours and voltages

| | |
|----------------------|--|
| Neon | Red, Amber, Green, Clear. 100/130V (marked 110V), 200/250V |
| LED | (marked 230V) |
| Filament lamp | Red, Yellow, Green 2.0/2.2V. Resistors for other voltages available. Red, Amber, Green, Clear and Blue. 6V, 12/14V, 24/28V. |

To create a catalogue no.:

Refer to the 2 columns below (terminal & type).
















Then state:

Lens colour, voltage and whether neon, LED or filament lamp.

- [*Additional Information / Temperature Rating Details](#)

[UL file E63363](#) [CSA file LR29381](#)

| TERMINALS | TYPE | DIMENSIONS |
|----------------------|----------------------------|--------------------------------|
| C 6.3 | (C) 0145 AA | |
| L W | (C) 1041 00 | |
| L W | (L) 1045 00 | Chrome bezel available |
| L W | (L) 0245 00 | Chrome bezel available |

| | | | |
|---|--|--|--|
| <p>L </p> | <p>L 2950 00</p>  <p></p> | <p> 8.0mm</p> <p> 0.8-1.6mm max.</p> <p> T85 °C</p> | <p>Chrome bezel available</p>  |
| <p>L </p> <p>C  6.3</p> | <p>(L) 0195 BB</p>  <p></p> | <p> 8.0mm</p> <p> 0.8-3.0mm max.</p> <p> T85 °C</p> |  |