

Product Datasheet

Product code: **ES5340.CR.BG**

Product type: High Precision Cutters

Made in: Switzerland

Description: The 5340 is a high precision cutter belonging to the small tapered cutter family. This type of geometry and head dimensions offer an advantage to access small areas. The semi-flush cutting edge is suitable to perform robust cuts. The 5340 is equipped with an ESD Ergo-tek slim handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.

Head description: Small, Tapered

Cutting edges: Semi-Flush

Cutting capacity: soft wire 0.20-1.20 mm (32-17 AWG)

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek Slim - Thermoplastic Elastomer + PP compound

Picture:



Dimensions:

OAL (A)	120.0 mm – 4.724 inch
Width	60.0 mm – 2.362 inch
Height	18.0 mm – 0.709 inch

Head dimensions:

Width (C)	10.0 mm – 0.394 inch
Thickness (D)	6.4 mm – 0.252 inch
B	9.0 mm – 0.354 inch
F	0.2 mm – 0.008 inch

