



Waterproof Connector



Specifications

Material

Housing: Nylon+GF

Contact: Brass

Plating: Base plated - Zinc 2um

Surface plated - Gold 1um

Operating Temperature : -40~125°C

Operating Humidity : 90%RH

Operating voltage: <50VAC/75VDC

Operating current: 10A

Insulation resistance: >1000MΩ

Contact resistance : <5mΩ

Dielectric intensity: AC1000V at 1minute

Suitable Cable outer Dia. $\varnothing 7.0 \sim \varnothing 10$

Waterproof class: IP68

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2017 by Conrad Electronic SE.