

[IMAGE]

## Product Information

Product Category	REFRIGERATION
Unit Barcode	5016368003626
Outer Carton Barcode	
Commodity Code	1081699
Country of Origin	TURKEY
Primary Colour	WHITE
Finish	PAINTED STEEL
Primary Material	PLASTIC
Warranty	2
Self Assembly	YES
Perishable Item	
Hazardous Item	

## General Product Specification

Voltage	230
Frequency	50
Wattage	187
Rated Current	0.85
Fuse Rating	13
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	2.5
Class	CLASS II
Conformity Markings	CE+UKCA

## Packaging &amp; Shipping Information

Product Dimensions H x W x D (mm)	1770	540	545
Packaged Dimensions H x W x D (mm)	1854	584	577
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			53
Unit Packaged Weight (Kg)			57.5
Carton Weight (Kg)			
EPS (Kg)	0.533	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.26	Card / Paper (Kg)	2.86
Aluminium (Kg)		Steel (Kg)	0.014

## Category Specific Technical Information

Type	BUILT-IN	Number of Freezer Compartments	1
Design Type	OTHER REFRIGERATING APPLIANCE	Number of Fridge Shelves	3
Gross Total Volume		Door Hinge Position	
Net Total Volume	242	Reversible Door	YES
Net Refrigeration Volume	179.5	Door Handle Colour	
Net Freezing Volume	63	Door Handle Material	
Energy Efficiency Index	100	Door Material	PAINTED SHEET METAL
Energy Rating	E	Door Opening Angle	90
Airborne Acoustical Noise Emission Class		Housing Colour	WHITE
Annual Energy Consumption	218	Lamp Rated Power	2
Climate Class	T/N	LED Lighting	YES
Minimum Ambient Operating Temperature	16	Power Failure Safe Storage	
Maximum Ambient Operating Temperature	43	Temperature Rise Time	8
Winter Setting	NO	Thermostat Temperature Range	2 ~ 8
Freezer Star Rating	4	Thermostat Type	MECHANICAL
Fast Freeze Facility	NO	Refrigerant Type	R600A
Freezing Capacity	3.3	Refrigerant Amount	35
Defrosting Type	A	RF: Back Panel Material	FULL METAL
Freezer Technology	FROST FREE		