


# 80114 Bendable probe Ø3.0mm, L=130mm with mini plug

## General

Toepassing	Sensor for general use
Construction	Oblique conical tip point
Handgreep	ABS plastic
Use	Primarily for gas, liquid and flame



## Sensor

Thermokoppel	Type K
Nauwkeurigheid	Volgens IEC 584-1
Response time	12 seconds
Max. tip temperature	600°C / 1112°F

## Sensor

Materiaal	Stainless steel
Probe lengte	130 mm
Tip diameter	3 mm
Connector	Miniature thermocouple connector, flat pins

## Options

Connector kleur	IEC / ANSI
-----------------	------------

