



Lite Highbay LED

HIGHBAY M.POWER 100/150/200W

High-efficiency industrial reflector suitable for high installation, with die-cast aluminium body and circular PMMA lens.

Order code 76305

EAN 8002219877666

Technical specifications

Absorbed Power	200 W, 150 W, 100 W
Supply voltage type	AC
Nominal voltage (AC)	230 Vac
Ambient temperature (min)	-20 °C
Ambient temperature (max)	40 °C
Insulation class	I
CCT light tone	4000 K
LED number	216
Beam angle	120 °
Colour consistency	SDCM2
CRI color rendering	>80
Diameter	299 mm
Ballast	For constant current LED
Efficiency	100 lm/W, 100 lm/W, 100 lm/W
Frequency (max)	60 Hz
Frequency (min)	50 Hz
Power factor	0.9
Glow wire strength	960 °C - 30s.
MTBF driver	30000 h
Luminaire flux	20000 lm, 15000 lm, 10000 lm
Mounting	Suspension
Voltage supply range (max)	253 V
Voltage supply range (min)	207 V

Installation and applications

Environment	Secondary Areas
Application	Industrial Areas




Mechanical specifications

Height	60 mm
Weight	3.4 Kg
Body material	Die-cast aluminium
Colour housing	Black
Cover material	Tempered glass
Protection grade IP	IP65
Protection grade IK	IK08

Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN IEC 60598-1:2021, EN 60598-2-1:1989, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013





Accessories



40910
CAMPANA 70-80° HB
MULTIPOWER