

Specifications




Pitch:	5.0mm
Type:	90° Wire Protector
Poles:	2 to 12
Rated Voltage:	300V
Rated Current:	10A
Operational Temperature:	-40°C to +105°C
Withstand Voltage:	2000V AC for 60s
Insulation Resistance:	500MΩ at 500V DC
Wire Range:	22-14AWG, 2.5mm ²
Wire Stripping Length:	5-6mm ± 0.5mm
Screw Size:	M3
Max. Torque Value:	0.5Nm
Wave Soldering:	260°C for 5s
Hand Soldering:	350°C for 10s



Colour and Materials

Housing Colour:	Green
Housing Material:	PA66
Flame Retardancy:	UL94-V0
Screw:	Zinc-plated steel (A3)
Wire Protector:	Stainless steel
Pin Header:	Tin-plated brass

Order Code	Poles	Order Code	Poles
21-3920	2	21-3984	8
21-3921	3	21-3985	9
21-3980	4	21-3986	10
21-3981	5	21-3987	11
21-3982	6	21-3988	12
21-3983	7		



Measurements are in mm unless stated otherwise.

