

M23 female 0° with cable

PUR 6x0.34+3x0.75 gy drag chain 10m

M23

Female straight

12-pole

9-pole used

for 6-way distribution box, 4-pole

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.


[Link to Product](#)

Illustration



1	white
2	green
3	yellow
4	gray
5	pink
6	red
11	brown 0.75 mm ²
9	blue 0.75 mm ²
12	green /yellow 0.75 mm ²

Female



Product may differ from Image

Form

23031

Technical Data

Operating voltage	125 V AC/DC
Operating current per contact	max. 7.5 A
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Locking of ports	Screw thread M23 × 1 mm

Cables

Cable number	355
No./diameter of wires	6×0.34 + 3×0.75 mm ²
Wire isolation	PVC (bl, wh, gn, ye, gr, pk, rd, gnye, br)
C-track properties	2 Mio.
Jacket Color	gray
Shore hardness outer jacket	85 ± 5A
Material (jacket)	PUR/PVC
Outer diameter	approx. 9.1 mm
Bend radius (fixed)	10 × outer Ø
Bend radius (moving)	12 × outer Ø
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+70 °C

General data

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1