



Datenblatt - Fiche technique - Data sheet


11.02.8805



ROLINE GOLD USB 2.0 Kabel, Typ A-B, 4,5m

ROLINE GOLD Câble USB 2.0, type A-B, 4,5m

ROLINE GOLD USB 2.0 Cable, A - B, M/M, 4.5 m



Pin Out

P1		P2
1	Red	1
2	White	2
3	Green	3
4	Black	4
Shell	Drain Wire	Shell

1. Cable UL2725 28AWG(7/0.127TC)*1P+24AWG(7/0.2TC)*2C+AEB(65%AL)
Jacket: Black Color with Braid, OD=4.5mm
2. Conn USB Type A M, Insulator: White, Pin Gold Plated 3u"
Shell: Gold Plated
3. Conn USB Type B M, Insulator: White, Pin Gold Plated 3u"
Shell: Gold Plated
4. Molding 45P, Color Black
5. Hood USB Type A M with USB 2.0 Mark(Laser), Aluminum, Color: Gold
6. Hood USB Type B M with USB 2.0 Mark(Laser), Aluminum, Color: Gold

P. / N.	Length
11.02.8802	1800 ⁺⁵⁰ ₋₀ mm
11.02.8803	3000 ⁺⁶⁰ ₋₀ mm
11.02.8805	4500 ⁺⁶⁰ ₋₀ mm

REV.	DATE	CONTENTS OF CHANGE	DESIGNER	TOL ±								APPROVAL	CHECK	DRAWING	DESIGN	DRAWING NAME	ROLINE USB 2.0 AM to BM Cable		
				RANGE	Plc	Met	Ins	Por	v	Cab	Pac						Gas	DIS	DATE
①				0~6	0.1	0.1	0.1	0.2	0.5	1	0.5	0.2	Allen	Allen		Allen	2016-05-6	11.02.8802 / 11.02.8803 /	ROO
②				6~30	0.1	0.1	.15	.25	1	1	0.5	.25					11.02.8805		
③				30~80	0.1	.15	0.2	0.3	2	1.5	1	0.3							
④				80~180	.15	.15	.25	0.3	2	2	1	.45							
⑤				180~315	.15	0.2	0.3	0.4	2.5	2	1	0.6							
				315~800	0.2	0.3	0.4	0.5	3	3	2	1.1							

SECOMP