

ARCA 507030



Sample photo

Order symbol: ARCA 507030
Product nbr: 8120031
Description: Cabinet, PC
Remarks: 2-point locking

EAN: 6418074086006
EI. number:
 Finland: 3424062
 Electric No. 8212095384
 Denmark:
 Electric No. Sweden: 2500119

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	500	700	300	MPP ARCA 5070	Mounting plate perforated (630x430x2 mm - 26x11 mm)
inch:	19.7	27.6	11.8	MPMP ARCA 7050	Mounting plate multiperforated (630x430x2 mm - □3.6 mm)
Materials:				MPX ARCA 7050	Mounting plate (630x430 mm)
Material:	Polycarbonate			DRS ARCA 507030	DIN rail frame set
Base colour:	RAL 7035 -light grey			IDS ARCA 5070	Inner door set
Cover colour:	RAL 7035 -light grey			PMK ARCA 70	Pole mounting kit
Gasket material:	Polyurethane			RCS ARCA 5070	Rain canopy set
Temperatures:				SBK ARCA 50	Support bar kit
Temperature °C (short term):	-40 ... 120 °C			SBK ARCA 70	Support bar kit
Temperature °C (continuous):	-40 ... 80 °C			DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060
Temperature °F (short term):	-40 ... 250 °F			DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060
Temperature °F (continuous):	-40 ... 175 °F				

Accessories:	
MPS ARCA 7050	Mounting plate (630x430x2 mm)

Rating:
 Ingress Protection (EN 60529): IP66
 Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 94 5VA
 Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:
 SGS Fimko
 Gost R

