

## **Product information**

## 71 72 610

## **Bolt Cutter**



- Cutting capacity up to 48 HRC hardness
- Robust cutting edges are additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Forged-in stopper with comfortable shock- absorber
- Good access due to very flat construction of head and joint area
- Ergonomically angled handles to minimise effort
- Sturdy non-slip two-colour multi-component handle sleeves
- Precise adjustment (12 positions) by eccentric bolt
  High cutting performance with minimum effort due to optimu
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Bolted cutter head, replaceable
  Joint: special tool steel, forged
- Joint: special tool steel, forgedHandles: steel tube, powder-coated
- Blade: chrome vanadium heavy-duty steel, forged, multi stage oilhardened

## You Tube

| General           |                            |
|-------------------|----------------------------|
| Article No.       | 71 72 610                  |
| EAN               | 4003773066767              |
| Head              | grey atramentized          |
| Handles           | with multi-component grips |
| Weight            | 2,550 g                    |
| Dimensions        | 610 x 122 x 34 mm          |
| REACH compliant   | does not contain SVHC      |
| RoHS compliant    | not applicable             |
| Technical details |                            |
| HRC 19            | Ø 9 mm                     |
| HRC 40            | Ø 8 mm                     |
| HRC 48            | Ø 7 mm                     |

34 mm

33 mm

technical change and errors excepted

Head thickness

Cutting edge length mm











