

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194340001](#)
Status: **Active**
Overview: [MX150L Industrial Sealed Connector System](#)
Description: MX150L Female Terminal for 10-12 AWG Wire, Metal Strip Carrier

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19432-001-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E152602

General

Product Family Crimp Terminals
 Series [19434](#)
 Application Power, Wire-to-Board, Wire-to-Wire
 Comments UL E152602
 Crimp Quality Equipment Yes
 Overview [MX150L Industrial Sealed Connector System](#)
 Packaging Alternative [19434-0003 \(Loose\)](#)
 Product Literature Order No 987650-2181
 Product Name MX150L
 UPC 822350193139

Physical

Durability (mating cycles max) 25
 Gender Female
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.841/g
 Packaging Type Reel
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 3.94mm-4.45mm
 Wire Size AWG 10, 12
 Wire Size mm² N/A

Electrical

Current - Maximum per Contact Contact Molex

Material Info

Reference - Drawing Numbers

Product Specification PS-19432-001-001
 Sales Drawing SD-19434-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

China RoHS

Search Parts in this Series

[19434 Series](#)

Use With

[19432 Female Receptacle](#)