

VELCRO® Brand
ONE-WRAP® Fasteners



SELF-GRIPPING FASTENERS FOR CORD CONTROL AND CABLE MANAGEMENT



Benefits

- Back-to-back fastener laminated without glue - no chemical residue
- Standard version available in 11 colors - great for electrical and network coding
- Fire retardant version meets certification requirements for MVSS 302, FAR 25.853 Appendix F Part 1 (a) (1) (i) and (ii), and UL 94-V2
- Designed for durability - ONE-WRAP® fasteners can be used over and over again
- Range of strap styles and sizes suit a wide variety of cord control applications



VELCRO® Brand
ONE-WRAP®

Applications



ONE-WRAP® STANDARD (888)

ONE-WRAP® FR (889)


Available Options

- Strap styles: See chart on far right
- Linear Widths: 3/8", 1/2", 5/8", 3/4", 1", 1 1/2", 2", 3", 4"
- Put-ups: 25 yard rolls or small crosswound spools

Performance

	Standard (888)	Fire Retardant (889)
Base Materials	Polypropylene hook and nylon loop	
Average Shear	23 PSI	29 PSI
Average Peel	0.5 PIW	0.6 PIW
Rated Load	18 pounds	18 pounds
Operating Temperature Range	0-222° F	0-222° F*
Cycle Life	Medium	Low-Medium

Colors



UL Air Handling Specifications











Fire retardant VELCRO® brand ONE-WRAP® straps meet acceptance as a Wire Positioning Device (16SA) in air handling spaces, in accordance with Section 300-22 paragraph (c) and (d) of the National Electric Code, and UL (Underwriter's Laboratory) requirements for a rating of 94-V2.

Qualified Configurations

Size	Die-cut straps: Width of head: 3/4" to 1 3/4" Width of tab section: 3/8" to 1" Length: 5" to 18"	Perforated linear tape: Width: 3/8" to 1" Length: 4" to 18"
Color	Black or Cranberry	
Minimum Contact Area	.75 square inches (on a die-cut strap with a 1/2" tab, this equals a 1 1/2" overlap)	
Maximum Operating Temperature	122°F (50°C)	
Designation	A label indicating product is UL-listed will be on the outer carton and the reel, and/or on the smallest put-up (e.g. poly bag, inner carton). A Certificate of Compliance referencing the specification is available, if requested.	

*Certified fire retardant up to 122°F

Choose the right strap style for your needs...

Size and Strap Style		Straps per Crosswound Spool
1/2" x 8"		1329
3/4" x 5"		1440
3/4" x 6"		1200
3/4" x 8"		900
3/4"x12"		600
3/4" x 18"		400
1" x 8"		675
1" x 12"		450
1/2" x 10"		1170
1 3/4" x 23 1/2"		230

Ask us about the VELCRO® Brand solutions for...

Medical & Orthopedics

- VELCRO® Brand Laminates
- VELCRO® Brand EVAPTEX™ Fabric
- VELCRO® Brand Double-Faced Loops

Packaging & Bundling

- VELCRO® Brand Bundle Ties
- VELCRO® Brand Easy Coins
- VELCRO® Brand High Technology Hooks

Displays & Exhibits

- VELCRO® Brand Knits
- VELCRO® Brand Qwik Ties
- VELCRO® Brand Woven Fasteners





ISO 9001
QMI-SAI Global

THE VELCRO COMPANIES ARE WORLDWIDE LEADERS IN FASTENING SYSTEMS, OFFERING A WIDE RANGE OF SOLUTIONS FROM STANDARD HOOK AND LOOP TO COMPLETE FINISHED PRODUCTS.

50 YEARS OF EXPERIENCE: WE ARE PROUD OF OUR HERITAGE IN INNOVATION, HAVING OVER 300 ACTIVE PATENTS TO OFFER BETTER SOLUTIONS TO SATISFY OUR CUSTOMERS' NEEDS.



TS 16949
QMI-SAI Global



North American Headquarters

United States

Velcro USA Inc.
406 Brown Avenue
Manchester, NH 03103
Tel: (800) 225 0180
Fax: (800) 835 2761
marketing@velcro.com
www.velcro.com

Canada

Velcro Canada Inc.
114 East Drive
Brampton, Ontario
L6T 1C1
Tel: (905) 791 1630
Fax: (905) 791 5329
canada@velcro.com
www.velcro.ca

Mexico

Velcro de Mexico, S.A. de C.V.
Ave. Industria No. 102 Nave IV-A
Col. Los Reyes Pueblo
Tlalnepantla de Baz
Edo. De Mexico C.P. 54090
Tel: (+52) 55 5005 3300
Fax: (+52) 55 5384 5413
salesmc@velcro.com
www.velcrodemexico.com

WORLDWIDE LOCATIONS

