



R.LA 1/4" long-reach metric 6-point sockets



Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Long-reach sockets for long recess or thread access.
- Available as rack set Ref RL.40E (3.2 --> 9 mm) and Ref RL.41E (10 --> 14 mm).
- Finish: bright chrome.



	A [mm]	Diameter [mm]	Diameter D1 [mm]	Length L [mm]	Length L1 [mm]	Hex Size [mm]	Weight [Kg]
R.10LA	0.4	14.3	14.3	50.5	7.9	6.0	0.041
R.11LA	0.4	16.0	16.0	50.5	7.9	6.0	0.054
R.12LA	0.5	16.8	16.8	50.5	8.4	6.0	0.05
R.13LA	0.5	18.2	18.2	50.5	8.4	6.0	0.059
R.14LA	0.6	19.2	19.2	50.5	10.2	6.0	0.068
R.3.2LA	0.1	12.0	5.8	50.5	1.8	6.0	0.018
R.4LA	0.2	12.0	6.8	50.5	2.0	6.0	0.018
R.5.5LA	0.2	12.0	8.1	50.5	3.0	6.0	0.018
R.5LA	0.2	12.0	8.1	50.5	2.3	6.0	0.018
R.6LA	0.2	12.0	9.4	50.5	5.6	6.0	0.018
R.7LA	0.3	12.0	10.9	50.5	7.1	6.0	0.027
R.8LA	0.3	12.0	12.0	50.5	7.9	6.0	0.027
R.9LA	0.4	12.8	12.8	50.5	7.9	6.0	0.032