

DATA SHEET


CAPSTAN WINCH CW 800 E + TROLLEY

for horizontal cable pulling

Item no.: 10138



Application images:



DATA

ITEM NO.	10138
WEIGHT CAPSTAN WINCH	32 kg
WEIGHT WINCH + TROLLEY + TRAP	41,20 kg
CAPSTAN (SMALL) PULLING FORCE	up to 800 kg at 4m per min
CAPSTAN (LARGE) PULLING FORCE	up to 400 kg at 8m per min
MOTOR CONNECTION	230 V 50 Hz
MOTOR DRIVE POWER	0,75 kWh 5,1 A
MOTOR SPEED	1400 U/min
DIMENSION WINCH	B 37 cm L 50 cm H 33 cm
DIMENSION TROLLEY	B 23,5 cm L 100 cm H 20,5 cm
STRAP LENGTH	3 m
EAN CODE	9120045475630

ADVANTAGES

- ✓ One person can pull up to 800 kg with the CW 800 E capstan winch
- ✓ Selectable traction force or traction speed 800 kg | 400 kg
- ✓ Small, compact, handy
- ✓ Many mounting options
- ✓ Safety rope guide
- ✓ Overload protection

DESCRIPTION

Ideally suited for horizontal pulling of one or more cables. Where several persons are needed for higher pulling loads on many sites, one person is sufficient to pull in the cables with the CW 800 E capstan winch by RUNPOTEC with a choice of **4 m/min | max. 800 kg or 8 m/min | max. 400 kg.**

The capstan winch can be fixed via the mounting holes or attached to solid objects with the enclosed strap. The trolley mounting rail also offers a very practical fastening option. It can be attached to the trailer hitch of a vehicle through the special coupling opening. It is also possible to mount the rail horizontally or vertically, and then simply hook in the CW 800 E capstan winch and fasten it using the two fixing bolts.



SAFETY INSTRUCTIONS:

Not suitable for vertical cable pulling, must not be used to carry or lift loads or persons.

Optimal area of application: for horizontal cable pulling.

Application video: a short, very informative application video can be viewed by scanning the QR code or on www.runpotec.com.

Scope of delivery: capstan winch CW 800 E incl. trolley mounting rail and strap

INFORMATION

Available separately:

Connection swivel

Item no.: 10176



Click here Productinformation

Polyester cable pulling rope

Ø 10 mm and 12 mm

Length from 120 m to 350 m

Polyester cable pulling rope on drum

Ø 10 mm and 12 mm

Length from 120 m to 350 m



Click here Productinformation